

nvacare brings the safety and convenience of a low bed into the Home Care Bed Series with the new IVC<sup>™</sup> Full Electric Low Bed. The split-spring design incorporated into the standard low bed profile combines the easy, one-person delivery of an Invacare® bed with the benefits of a low bed, where rails are not desirable or appropriate, but injuries from falling out of bed are still a concern. The IVC Low Bed ends are fully compatible with existing Invacare full-electric bed frame inventories and the IVC drive shaft, simplifying inventory management for providers and long-term care facilities.





Low Bed in highest position.



Low Bed in lowest position.

## **HIGHLIGHTS**

- · 9.5" minimum floor-to-bed deck height
- · 20" maximum floor-to-bed deck height
- · Patent-pending
- · 450 lb. total weight capacity
- UL962 and CSA approved

SPECIFICATIONS					
5410LOW IVC Full Electric Low I	410LOW IVC Full Electric Low Bed				
Bed height*	9.5" min 20" max.				
Sleep surface	36"W - 80" L				
Overall bed	36"W - 88" L				
Limited warranty					
All welds	Lifetime				
Mechanical/electrical	3 years				
* Massumment from floor to had dock					

Measurement from floor to bed deck

Model no.	Description
5000IVC	Head Spring Section
Carton size	44" W x 36" L x 8" D
Shipping weight	44 lb.
5490IVC	Foot Spring Section Full-Electric
Carton size	47" W x 37" L x 8" D
Shipping weight	76.5 lb.
5301LOW	Universal Low Bed Ends
Carton size	39" W x 25" L x 7" D
Shipping weight	55 lb.

# UNIVERSAL BED END **FEATURES**

## **BENEFITS**

•	IVC™ Universal Low Bed End, IVC Headspring • and IVC Footspring	Interchangeable with the original Invacare® Home Care Bed	
•	High impact bed end panels •	More durable, impact and scratch resistant; washable for easy	ı

	9 1			
•	Universal Low Bed End	•	Can be used as either the headboard or footboard on the Low Bed	
•	Caster tread	•	Better tracking with non-marring material	

# **ELECTRONICS**

#### **FEATURES BENEFITS**

•	DC low voltage, compact motor system	•	Quiet motor operation, and fast cycle time on lowering height of
			bed for efficient bed set-up

- Washable motor system and frame Motor system with waterproof enclosures is rated IP66. Washable with standard water pressure. The bed should not be power washed.
- Color-coded connections on junction box Easier maintenance
- Double-insulated junction box Provides extra protection
- Ergonomic hand pendant Comes with durable strain relief and heavy-duty cord. Waterproof casing for easy cleaning, conveniently attaches to bed sheet with clip or bed rail with hand pendant cradle (sold separately)
- Hand pendant cradle Available for convenient storage of hand pendant (part no. 26975)
- Electrical/mechanical limited warranty 3 years – longest warranty in the industry
- Interchangeability Simplifies storage, reduces inventory complexity



**Invacare Corporation** www.invacare.com

#### **USA**

One Invacare Way Elyria, Ohio 44035-4190 (800) 333-6900

### Canada

Invacare Canada Inc. 570 Matheson Blvd. E. Unit 8 Mississauga, Ontario L4Z 4G4 Canada

Invacare and the blue medallion design are registered trademarks and Yes, you can. and IVC are trademarks of Invacare Corporation. Specifications are subject to change without notification.

© 2005 Invacare Corporation

Form No. 04-173 Rev. 05/05



"Invacare says 'Yes, you can.™ and I couldn't have said it better myself,