



NuScan 510

5-Megapixel 11" x 17" Visual Presenter



Model: NuScan 510 QuickGuide English

www.adesso.com

①

LIMITED WARRANTY

Adesso provides a one year limited warranty for all of its products against defects in material and workmanship.

During this period, Adesso will repair or replace any product which proves to be defective. However, Adesso will not warranty any product which has been subject to improper freight handling, shipping abuse, neglect, improper installation or unauthorized repair. The warranty will not cover products installed with components not approved by Adesso and products where the sealed assembly trace has been broken.

If you discover a defect, Adesso will, at its option, repair or replace the product at no charge to you provided you return it during the warranty period with freight charges pre-paid to Adesso. Before returning any product, you must obtain a Return Merchandise Authorization number (RMA). This RMA # must be clearly marked on the outside of the package you are returning for warranty service. Be certain to also include your name, shipping address (no PO Boxes), telephone number, and a copy of the invoice showing proof of purchase in the package.

SUPPORT

We have listed most of our FAQ's (Frequently Asked Questions) at: <http://www.adesso.com/faqs.asp>. Please visit our FAQ Service & Support pages before you contact our E-mail or Telephone Support.

Email Support: If our FAQ's do not help you resolve your issues, please email support@adesso.com.

Telephone Support:
Toll Free: (800) 795-6788
9:00AM to 5:00PM PST Monday - Friday

②

INTRODUCTION

The Adesso NuScan 510 5-Megapixel Visual Presenter (A3 Size) is the ideal tool for presentations, image capturing and video recording. With this visual presenter and your computer, you can capture real-time images of 3D objects (up to 11.7 x 16.5 x 15" in size), magazines, books, documents, pictures and business cards and present through a monitor or projector. The unique down-facing lens makes repetitive image capturing, demonstrations, tutorials and lectures comfortable and simple. Along with these great features, use the included ArcSoft® Medialmpression 3 HD software with your NuScan 510 to take snapshots or record videos of just about anything, easily edit both images and videos with the advanced editing tools, plus enjoy the convenience of sharing files directly from software. ABBYY® FineReader software also accompanies your NuScan 510 and offers an Optical Character Recognition (OCR) function that scans your captured image and extracts text, making it easy to share information without retyping. The NuScan 510 combines all the great features of today's most popular image capturing devices into one powerful product.

SPECIFICATIONS


- Image Sensor: 5.0 Megapixel CMOS Color Sensor
- Interface: USB 2.0
- Resolution: Up to 2592 x 1944
- Image File Format: TIFF, JPG, BMP & PNG
- Image Capture Speed: 1 second
- Document File Format: DOC, TXT, PDF & XLS
- Video File Format: WMV
- Shooting Area: Up to A3 Size - 11.7 x 16.5" (297 x 420mm)
- Focal Length: 4" to 15" (101 mm to 381 mm)
- Focus: Manual
- Frame Rate: Up to 30 frames per second (max)
- LED Lights: 14
- White Balance: Auto

REQUIREMENTS

- Operating System: Windows® 7, Windows® Vista & Windows® XP
- Connectivity Interface: USB 2.0 Port

③

CONTENTS



④


DESCRIPTION




⑤

INSTALLATION

1. Plug the USB connector into an available USB port on your computer and connect the other end of USB cable to the back of NuScan 510 Visual Presenter.




2. NuScan 510 will connect automatically to your computer (NuScan 510 is a driverless device when used with Windows® 7, Windows® Vista or Windows® XP operating systems). Your computer will recognize device as **USB 2.0 Camera** under Imaging Devices in Device Manager menu.




⑥

SOFTWARE INSTALLATION

1. Insert the enclosed Software CD into your computer's CD-ROM. The installer program should start automatically. (Note: If installer program does not start automatically, browse CD content and launch setup.exe)



2. Follow the on-screen instructions to complete installation.
3. When prompted enter your preferred user name and the license key located on the sleeve of software CD envelope.



License Key

⑦


GETTING START

1. To begin using Medialmpression HD software with NuScan 510, click on the Medialmpression HD Edition shortcut installed on your computer desktop.

2. In software main menu select **Pictures** for image snapshots tools or **Videos** for video recording tools.




3. To begin using Nuscan 510 with software, select **Import** from bottom drop down menu, then select **WebCam**.



⑧

4. If you would like to adjust **Picture** or **Video** settings, click on to adjust **Picture** settings or click to adjust **Video** settings. For higher resolution, select preferred resolution from **Snapshot** drop down menu for **Pictures** or select preferred resolution from **Video** drop down for **Videos** (higher resolution may cause a delay in video recording option).



Note:

1. To obtain the best image/recording results place NuScan 510 and objects on Reversible Soft Position Pad.
2. Preview image in software and adjust the Focus Wheel as needed to obtain clear images of objects.
3. If natural light source is not bright enough, turn on the built-in LED lights to increase the brightness.
4. For more software details refer to the software manual(s) in the Software CD.

⑨