

This Datasheet for the

IC670ALG620

RTD 4 Channel Isolated 3 or 4 Wire Input

http://www.qualitrol.com/shop/p-14496-ic670alg620.aspx

Provides the wiring diagrams and installation guidelines for this GE Field Control module.

For further information, please contact Qualitrol Technical Support at

1-800-784-9385

support@qualitrol.com

The RTD Analog Input Module (IC670ALG620) accepts inputs from 4 independent 3-wire and/or 4-wire platinum, nickel, nickel/iron, or copper RTDs.

Module features include:

- Selectable resistance measurements in tenths of ohms, tenths of degrees Fahrenheit, or tenths of degrees Celsius
- Individual channel configuration
- Selectable resistance ranges: 0 500 ohms and 0 3000 ohms
- Selectable RTD input as resistance or temperature (Celsius or Fahrenheit)
- Reportshigh/low, underrange/overrange, open wire and input short alarms.
- Uses optional discrete inputs and outputs for status and control.
- Two data acquisition rates based on 50 Hz and 60 Hz line frequencies
- Configurable channel activation



Power Sources

No loop power is required for this module. The excitation current for the RTDs is provided by the module, which automatically matches the excitation current to each configured RTD type.

LED

A single indicator shows module status:

- ON: normal operation
- Intermittent flashing: module fault
- OFF: loss of backplane power or fatal fault

GFK-1206D June 1997

46722

Module Operation

The RTD Input Module accepts four inputs from three-wire or four-wire RTDs and converts the input level to a digital value. Input spans support a variety of RTD types, as listed in the Module Specifications section.

The analog/digital converter reads the voltage generated by each of the four inputs. The A/D converter converts the differential measurement into a binary value (15 bits plus sign), which is read by the block's microprocessor. The microprocessor sets the gain required in the analog/digital converter for each individual input. The gain is based on the RTD type that has been configured for that input.

The microprocessor selects the input by means of a solid state, optically-coupled multiplexer. Three measurements are made for each input: Excitation current, RTD resistance including field wire drop, and field wire drop. From these three measurements, the module calculates the RTD resistance. A DC/DC converter circuit isolates the field side from the logic circuits.



Calibration

The module automatically performs A/D calibration at powerup. Automatic calibration is then repeated every minute to compensate for changes in the ambient temperature.

The module stores the calibration constants for each gain in RAM memory. This data can be read and changed if necessary.

GFK-1206D June 1997

June 1997

3

Host Interface

The RTD Input module has the following data types:

- 4 analog inputs (4 words)
- **32** bits of discrete input data for module and channel status (use of this data is optional)
- 8 bits of discrete output data for fault clearing to the module (also optional)
- Analog output data defaults to a length of 0, and should NOT be used for most applications.

A starting reference and length in the Bus Interface Unit (BIU) data tables for each data type is selected during module configuration. Depending on the configuration that has been set up for each RTD, the input data can be reported as tenths of ohms, tenths of degrees Fahrenheit, or tenths of degrees Celsius.

This module exchanges data with a BIU in the same manner as other types of I/O modules—it provides all its input data and status bits when requested by the BIU, and receives fault-clearing commands from the BIU via its assigned output bits. Note that the BIU can be configured not to send status data over the network.

The module can also be configured for "Group" data transfer with the BIU or with other intelligent devices in the same Field Control station. Group data transfer, and the steps for configuring it, are described in the *Bus Interface Unit User's Manual.*

UnitsSelected	IntegerRanges	EngineeringUnits Ranges		
Tenths of Degrees	-32767 to +32767	-3276.7 to +3276.7		
Tenths of Ohms	0 to 65535	0 Ohms to 6553.5 Ohms		

Compatibility

This module must be used with a Bus Interface Unit revision 2.0 or later.

Module Configuration Overview

Like other Field Control modules, the RTD Input module is usually configured from the Bus Interface Unit, using a compatible hand-held programmer. The module will also accept configuration data from the bus when used in a system that supports such configuration. The table below summarizes configuration choices and defaults. The module will power up with the default configuration settings. For configuration instructions, refer to the *Bus Interface Unit User's Manual*.

Module Parameter	Description	Default	Choices		
AnalogInput Data Length	Word length of the module's analog input data in the BIU's analog input (AI) data table.	4	0-4		
AnalogInput DataReference	Starting offset for the module's analog input data in the BIU's analog input (AI) table.		userselectable		
Discrete Input Data Length	Bit length for the module's optional status data in the BIU's discrete input (I) table.	32	0–32		
Discrete Input Data Reference	Starting offset for the module's status data in the BIU's discrete input (I) table.		userselectable		
DiscreteBit length for the module's optionalOutput Datafault-clearing bits in the BIU's discreteLengthoutput (Q) table.			0-8		
Discete Output Starting offset for the module's optional Data Reference fault-clearing bits in the BIU's discete output table. fault-clearing bits in the BIU's discete			userselectable		
AnalogOutput Data Length			0-4		
AnalogOutputStarting offset for the module's analog output data in the BIU's AQ table.			userselectable		
Line Frequency	e Frequency Specifies the line frequency.		50 Hz, 60 Hz		
Channel Active	Channel Active Specifies if the channel should return data and alarms. If a channel is "inactive" space is still allocated for it.		Inactive (off), Active (on)		
Units	The conversion type for each RTD.	Deg C	tenths of ohms, tenths of degrees C, or tenths of degrees F		
RTD Type	RTD Type The type of RTD used for each channel.		10 PT, 25 PT, 25.5 PT 392, 100 PT 385, 100 PT 3902, 100 PT 392, 100 PT 3923, 100 PT 3916, 1K PT 375, 10 CU, 10 CU 427, 50 CU 427, 100 CU 427, 100 NI, 100 NI 618, 120 NI 672 604 NI/FE518, 1K NI/FE527, 500 Ohm, 3000 Ohm		
Wire Type The type of field wiring for each RTD.		3 Wire	3 Wire, 4 Wire		
Alarm Low	The low alarm limit for the channel, in engineering units.	-200	-32,768 to +32,767		
Alarm High	The high alarm limit for the channel, in engineering units.	800	-32,768 to +32,767		
Resistance	An optional resistance adjustment, in tenths of ohms.	0	0 to 3276.7		

GFK-1206D June 1997

GFK-1206D June 1997

Module Features

Channel Active

Each channel can be configured as either active or inactive.

If a channel is inactive, it is not scanned and a value of 0 is returned to the BIU.

If a channel is active, and the configured analog input data length is not long enough to accommodate the data for a particular channel, the data for that channel is still processed, since the response to a group command may be used to transmit that channel's data to the BIU.

Low Alarm Limit and High Alarm Limit

Each input channel can have a low alarm limit and a high alarm limit. If an input reaches one of its limits, the module reports the actual value and sends the appropriate diagnostic bit in the discrete input table of the BIU. Alarms do not stop the process or change the value of the input.

Alarm limits can be set anywhere over the dynamic range of the signal. The range for each is -32,768 to +32,767. The high alarm limit must be greater than the low alarm limit. If alarm reporting is not wanted, alarm limits can be set beyond the dynamic range of the signal so they will never be activated.

Input Selection to Include RTD Type

Each input channel can have a different RTD type, selectable from a list of many different RTDs.

If the actual RTD resistance does not match the defined type, an adjustment factor can be configured in tenths of ohms.

Selection	Selection Comments		Selection Comments		Comments
10 PT	10 Ohm Platinum (PT)	100 PT 3916	100 Ohm Platinum, α =.003916	100 NI 618	100 Ohm Nickel At $0C$, DIN43760, α =.00618
25 PT	25 Ohm Platinum IPTS-68	1K PT 375	1 KOhm Platinum, α=.00375	120 NI 672	120 Ohm Nickel, at 0C, α =.00672
25.5 PT 392	25.5 Ohm Platinum, α =.00392 at 0C Lab Std	10 CU	10 Ohm Copper, at 25C, IPTS-68	604NI/FE518	604 Ohm Nickel/Iron, at 0C, α =.00518
100 PT 385	100 Ohm Platinum, DIN43760, α =.00385	9.035 CU 427	9.035 Ohm Copper, at 25C, α=.00427	IKNI/FE527	1 KOhm Nickel/Iron, at 70F, α =.00527
100 PT 3902	100 Ohm Platinum, α =.003902	50 CU 427	50 Ohm Copper, α=.00427	500 OHM	Select UNITS of 1/10 Ohms
100 PT 392	100 Ohm Platinum, α=.00392 IPTS-6 8	100 CU 427	100 Ohm Copper, α=.00427	3000 OHM	Select UNITS of 1/10 Ohms
100 PT 3923	98.13 Ohm Platinum, α =.003923	100 NI	100 Ohm Nickel, IPTS-68		

RTD Limits

The table below lists the ohms and temperature limits for different RTD types.

RTD Type	Low Ω Limit	HighΩ Limit	Low Temp. C	High Temp. C	
10 Ohm Copper @ 25C	6.13600	14.8200	-75.00	150.00	
10 Ohm Platinum @ 25C	7.02000	37.2599	-70.00	1000.00	
25 Ohm Platinum	4.14500	74.3089	-201.1111	537.77	
100 Ohm Nickel	80.88890	147.7700	-40.00	140.00	
1 KOhm Platinum, α=.00375	199.4880	2754.620	-200.00	500.00	
100 Ohm Platinum α =.00385	27.01	389.936	-180.0	850.0	
100 Ohm Platinum, α=.003902	93.5400	135.000	-17.7777	99.9999	
100 Ohm Platinum IPTS68 (PA)	26.5	327.744	-200.0	630.0	
100 Ohm Platinum SAMA-RC21-4 (PC)	26.5	311.874	-200.0	600.0	
100 Ohm Platinum JISC-1604-'81	26.5	323.780	-200.0	620.0	
25.5 Ohm Platinum Lab Std (PJ)	4.50	83.575	-200.0	630.0	
9.035 Ohm Copper (CA)	6.05	16.400	-100.0	260.0	
50 Ohm Copper (CB/2)	28.379	105.787	-100.0	260.0	
100 Ohm Copper (CB)	56.757	211.574	-100.0	260.0	
100 Ohm Nickel (NB)	69.520	223.221	-60.0	180.0	
120 Ohm Nickel (NA)	66.600	380.310	-80.0	260.0	
604 Ohm Nickel/Iron(FA)	372.789	1318.722	-100.0	204.0	
1 KOhm Nickel/Iron(FB)	566.576	1985.891	-100.0	204.0	

Module Specifications

Number of Channels	Four3-wireand/or4-wireRTDs			
Scan time	60 Hz: approximately 210 milliseconds per point 50 Hz: approximately 230 milliseconds per point,			
Fault detection	Open RTD, input short, underrange, overrange, and high/lowala			
Normal mode rejection	60dB, at 50/60 Hz, 100% span			
Common mode rejection	120 dB at 50/60Hz, 100 ohm imbalance			
Common mode voltage	250 Vrms (350 VDC or peak AC)			
Normal mode voltage	100% overrange DC or peak AC operational 28 VDC or peak AC maximum			
Isolation:				
User input to logic, user input to frame ground.	1500 VAC for 1 minute, 250 VAC continuous.			
Channel to Channel	250 VAC continuous.			
Current drawn from BIU power supply	190 mA maximum			
DigitalResolution	15 bits plus sign			
Operating temperature range	0 to 55 Degrees C ambient			
Channel Characteristics				
RTD types	10, 25, 100, and 1000 ohm platinum 10 and 100 ohm copper 100, 50, and 120 ohm nickel 604 ohms and 1000 ohms nickel/iron			
Resistanceranges	0 to 500 ohms 0 to 3000 ohms			
Accuracy, at 25 C	RTD: +/-0.15% of reading, +/-0.3 to 0.5 degree Celsius, dependent on type			
Temperature sensitivity (0 to 60C)	+/-0.004% of reading, +/-1.5µV per C referred to input			
Maximumleadresistance	5 ohms per lead			

Keying Locations

Optional keying locations for the RTD Module are:

KeyingLocations									
Α	В	С	D	Е	F	G	Н	J	K
7			~				~	~	

Field Wiring

The following illustration shows connections for 3-wire and 4-wire RTDs.



No loop power is required for this module. The excitation current for the RTDs is provided by the module, which automatically matches the excitation current to each configured RTD type.

I/O Terminal Block Terminal Assignments

The Terminal Block with box terminals (IC670CHS002) has 25 terminals for each module. Each accommodates one AWG #14 (avg 2.1mm² cross section) to AWG #22 (avg 0.36mm² cross section) wire, or two wires up to AWG #18 (avg. 0.86mm² cross section). When an external jumper is used, wire capacity is reduced from AWG #14 (2.10mm²) to AWG #16 (1.32mm²).

The I/O Terminal Block with barrier terminals (IC670CHS001) has 18 terminals per module. Each terminal can accommodate one or two wires up to AWG #14 (avg 2.1mm² cross section).

The I/O Terminal Block with Connectors (IC670CHS003) has one 20-pin male connector per module.



GFK-1206D

June 1997

Diagnostics

The RTD module performs diagnostics and provides the diagnostic data to the BIU using its configured discrete input (I) references, starting at the configured reference offset.

The RTD sets the appropriate bit when a diagnostic condition is detected. The bit remains set until cleared.



Clearing Faults and Alarms

Four optional discrete output bits in the BIU's discrete output (Q) table can be used to clear module faults and alarms.

Setting the discrete output bit for an RTD clears all diagnostic bits for that RTD that may be set.

Output Command Bits to Clear Diagnostics



GFK-1206D June 1997