

World Class

Universal power clamps



standard **IEC**
61010
Cat. I
600 V



**Whether you have a single-phase or three-phase network,
nothing will be hidden from you any more!**

- Types of measurement: AC and AC+DC TRMS voltage, AC and AC+DC TRMS current, single- and three-phase power, Energy, Frequency
- Three-phases input in a single unit
- Measurement of the power factor and determination of the compensation capacitors
- Analogue retransmission of the measurements via adapters
- Data capture and subsequent processing on PC (adapter and software available as options)
- Dual display to read off the results more quickly

Universal power clamps - MX 2040 and MX 240

Signal characterisation

When configured in Surveillance (SURV) mode, the clamp can almost characterise the signals. It can thus detect peaks of a minimum width of 1 m.sec (in V and A), optimising the range choice, according to the form of the signal. In addition to this, the Minima, Maxima or Average can be measured (in A, V, kVA, kW, kVAR and Ω). The latter is a sliding calculation over 16 values.

Better and quicker measurement

These clamps have been designed to facilitate and optimise measurement: HOLD mode freezes the display and improves reading statements; AUTO OFF mode puts the clamp onto standby and increases its autonomy; AUTO/MANUAL mode allows the user to opt for automatic or manual change in range. Finally the CAL button offsets the zero when measuring current.

Three-phase measurement

For balanced three-phase networks, the clamp automatically detects the presence of the three phases and gives the result immediately. For unbalanced three-phase networks, measurement has to be taken on each of the phases in succession. In all cases, the direction of rotation is indicated which avoids any difficulties with reversed connections.

Measurement of the power factor

By determining the phase shift between voltage and current, the clamp can automatically calculate the compensation capacity needed to restore the power factor to a value specified by the user. If the value obtained is not standard, it is possible to modify it: the clamp will then calculate the influence of this modification on the power factor. This measurement is available in both single and three-phase.

High contrast display

The display is split into two parts and enables results to be read off rapidly; the top zone is reserved for the function selected by the rotating switch and the bottom zone gives the result of secondary functions (Peak, Min. Max. etc.)



The display is wide, easy to read and all the necessary information can be taken in at a glance.



Hard-wearing and robust, the HA1339 case is used to store the clamp with leads, touch-pins and other accessories. Ideal for tests out on site or in the factory.

Measurement of kWh

Thanks to its internal clock and power measurement capacity, the clamp can total up measurements from the time of entering into a function and then calculate the energy in kWh.

Safety mains supply

Every detail of the clamp and adapters has been thought out: an option can be added to connect them to an IEC 61010 Cat. III mains supply. Measurement sessions without any autonomy constraints are then possible. Three models are available according to the country of use: Europe, the United Kingdom and the United States.



ADP1



ADP2





ADP3

The adapters for the MX 2040 and MX 240 clamps replace the lide of the battery compartment. In this way, the careful design and electric safety of the clamp is retained.


A veritable acquisition station.

The ADP 3 option transforms the clamp into a veritable acquisition station. In fact, the performance of the latter is enhanced by a 512 measurement memory which has a programmable rate of memorisation (Datalog mode), the digital transmission of displayed measurements by means of an RS 232 link and a graphic and digital data processing programme (SX-DCOM). This programme can manage up to four clamps simultaneously which is particularly advantageous for three-phase measurement. Furthermore, it enables the clamp to be configured or adjusted by remote control using a PC.



Analog output of signals

The MX 2040 and MX 240 clamps have ADP 1 and ADP 2 adapters and an analog output which is the image of the values measured. There are two output modes, with different update rates: instantaneous mode (INST.) and Display (DISP.) modes.



| CHARACTERISTICS - ANALOG OUTPUT | ADP 1 | ADP 2 |
|---------------------------------|------------------------------------|-----------------------------------|
| Sensitivity - Current | | |
| INST mode | 0.25 to 25 mV/A | 0.25 to 25 mV/A |
| DISP mode | 0.5 to 50 mV/A | 0.5 to 50 mV/A |
| Sensitivity - Voltage | | |
| INST mode | - | 1.333 to 2.5 mV/V |
| DISP mode | - | 1.333 to 2.5 mV/V |
| Sensitivity - Power | | |
| INST mode | - | - |
| DISP mode | - | 0.75 to 750 mV/k* |
| Sensitivity - Resistance | | |
| INST mode | - | - |
| DISP mode | - | 0.75 to 7.5 mV/Ω |
| Max. output current | 1 mA | 1 mA |
| Full scale | 1.5 V (0.75 V for INST current) | 1.5 V (0.75 V in INST current) |
| Output resistance | < 10 Ω | < 10 Ω |
| Sampling | | |
| INST mode | 61 µsecs | 61 µsecs |
| DISP mode | 500 msecs | 500 msecs |
| Output protection | 20 V max | 20 V max |
| Power supply | By clamp or mains supply (Option) | By clamp or mains supply (Option) |

*kVA, kW or kVAR, according to the type of measurement chosen

SX-DCOM software minimum configuration

- PC or compatible computer with 80386 or higher and 25 MHz minimum clock speed (80486 33 MHz recommended)
- VGA resolution or higher
- Mathematical coprocessor
- Min. 4 MB RAM (8 MB recommended)
- 2.5 MB hard disk capacity free
- Microsoft Windows 3.1 or later
- MS-DOS version 3.1 or later.

| GENERAL CHARACTERISTICS | MX 2040 | MX 240 |
|----------------------------------|---------------------|--------------------|
| Jaw opening | 55 mm 22x64 bars | 55 mm 7x52 bars |
| Dual display (up to 3000 counts) | yes | yes |
| Size of digits | 11.5 and 7 mm | 11.5 and 7 mm |
| Measurement rate | 2 per sec | 2 per sec |
| Detection of rapid peaks | 1 msec | 1 msec |
| Digital adjustment | yes | yes |
| Power supply: 9 V battery | 8LF22 | 6LF22 |
| Automatic cut-out | After 3 mins | After 3 mins |
| Autonomy (alkaline battery) | 40 hrs | 40 hrs |
| IEC 61010 safety | Cat. IV 600 V | Cat. IV 600 V |
| Temperature for use | -10 to 55°C | -10 to 55°C |
| Storage temperature | -20 to 75°C | -20 to 75°C |
| Relative humidity <80% | yes | yes |
| Dimensions | 285 x 90 x 50 mm | 270 x 90 x 50 mm |
| Weight, with battery | 610 g | 550 g |
| Warranty | 1 year | 1 year |

| TECHNICAL CHARACTERISTICS | MX 2040 | MX 240 |
|---|---|---|
| • AC, AC+DC Current | | |
| Ranges | 200 - 2000 A | 20 - 200 A |
| Resolution | 0.1 to 1 A | 0.01 to 0.1 A |
| Basic accuracy | 1%R + 8D | 1%R + 8D |
| Min. current measurable | 1 A | 0.1 A |
| • DC Current | | |
| Ranges | 300 - 2000 A | 30 - 300 A |
| Resolution | 0.1 to 1 A | 0.01 to 0.1 A |
| Basic accuracy | 1%R + 8D | 1%R + 8D |
| • DC, AC, AC+DC (TRMS) Voltage | | |
| Ranges | 600 - 1000 V _{DC} 400 - 750 V _{AC} | 600 - 1000 V _{DC} 400 - 750 V _{AC} |
| Resolution | 0.1 to 1 V | 0.1 to 1 V |
| Basic accuracy | 0.5%R + 8D | 0.5%R + 8D |
| Input impedance | 970 kΩ | 970 kΩ |
| • Power (active, reactive, apparent) | | |
| Ranges* | 20k - 200k - 2000k | 2k - 20k - 200 k |
| Resolution | 0.01 to 1 k | 0.001 to 0.1 k |
| Basic accuracy | 1.5%R + 16D | 1.5%R + 16D |
| • Active energy | | |
| Ranges | 20 - 200 - 2000 kWh | 20 - 200 - 2000 kWh |
| Resolution | 10 Wh | 1 Wh |
| Basic accuracy | 1.5%R + 10D | 1.5%R + 10D |
| • Power factor (cos φ) | | |
| Ranges** | 0 to 1 | 0 to 1 |
| Basic accuracy | 0.01 + 2° (50/60 Hz) 0.01 + 3° at 400 Hz | 0.01 + 2° (50/60 Hz) 3° at 400 Hz |
| • Frequency | | |
| Ranges | 20 Hz - 200 Hz - 2 kHz | 20 Hz - 200 Hz - 2 kHz |
| Resolution | 0.01 Hz to 1 Hz | 0.01 Hz to 1 Hz |
| Basic accuracy | 0.3%R + 1D | 0.3%R + 1D |
| • Resistances | | |
| Ranges | 200 Ω - 2000 Ω | 200 Ω - 2000 Ω |
| Resolution | 0.1 to 1 Ω | 0.1 to 1 Ω |
| Accuracy | 1.0%R + 5D | 1.0%R + 5D |
| Test current | 0.5 mA. approx. | 0.5 mA approx. |
| Max. voltage with open circuit | 80 V | 80 V |
| • Continuity | | |
| Detection threshold | < 30 Ω | < 30 Ω |
| Response time | 10 msecs | 10 msecs |

* For Active power: Watts (W)
Reactive power: reactive Volts-Amps (Var)
Apparent power: Volts-Amps (VA)

**For V > 60 V, and I > 3 A (MX 240) or I > 30 A (MX 2040) phase shift of voltage and current signals and zero reset.

Characteristics subject to modifications according to technological developments.

metrix
Division of Chauvin Arnoux

AUSTRIA
Slamastrasse 29/3
1230 Wien
Tel. : 01 61 61 9 61
Fax : 01 61 61 9 61 - 61



Accessories and ordering information

Accessories included

Each model comes with 3 measurement leads, 3 touch-pins, 3 alligator clamps, 2 batteries, a verification certificate and a user's manual.

Accessories on option

HA1268B ADP1: analog output - current
HA1260B ADP2: analog output for all measurements taken
HA1261B ADP3: RS 232 interface and SX-DKOM software
AA2850 Mains supply: Europe
AA2851: Mains supply: UK
AA2852: Mains supply: USA

To order

MX0240A MX 240 power clamp
MX2040A MX 2040 power clamp
MX0240AM MX 240 in a case with main supply and ADP 1
MX2040AM MX 2040 in a case with main supply and ADP 1

For assistance and ordering