

FOLLOW SPOT LIGHT

RG-F02

User Manual

Please read over this manual before operation the light

Warn

Welcome to use BOB 1200W Follow Spot Light . In order to bring safer and better service , please read this user manual carefully before you run the light . Please follow the operation to avoid the injury to body and the damage to the light .

Part A : Product Introduction

BOB 1200W follow spot light use the high quality aluminum shaped board and iron board as the cover . With its latest cover design and optical system design % 6 pieces strong fan ., it keeps its expected high heat radiation and high brightness character . The advanced electrical PCB drive the 3 pieces micro electrical motor for the wash , strobe , dimmer zoom effect . The focus is adjustable , very easy and quick to handle .

Part B :Operation

After open the box , please check if the item gets any damage during the shipment . For example : the screw loosen , lens broken . After the check , please follow the step below :

- (1) Please set the light on the stand , adjust the scan angel .
- (2) Connect the proper power and ground wire , and then turn on the power .
- (3) After the power on , the inside PCB will start its automatic checking for 40 seconds . Only after the check , you can start the

operation .

- (4) During the operation , please press the button according to its function .

Part C :Notice

- (1) The lamp belongs to HMI series . After the power on and light get full brightness , the power can be turned off . After the power off for several minutes for the lamp get cool , we can turn on the power again . Otherwise the lamp' life time will be shorten much .
- (2) Please do not look the light direct to avoid eye injury .
- (3) During the installation and maintain , please make sure the power is off .
- (4) Please do not use other lamp with different specification .

Part D : Technical Details

Power Supply : AC200V-220V

Power : 1300W

Frequency ; 50-60HZ

Anti Power : 1.5KV

Insulated Resistance : 7.2M

Distance :4M-6M

Safe standard : CE20/30 3rd Level

Strobe : 1 to 7 times per second

Working : Indoor

Size : 120*44*29CM

Weight : 42

Lamp : HMI1200W