



## GATEKEEPER® INERT GAS PURIFIERS

*Cost-effective, environmentally friendly gas purification*



# *cost-effective, environmentally friendly gas purification*

## Overview

Available for point-of-use, area and bulk applications, GateKeeper® inert gas purifiers are designed for use with N<sub>2</sub>, He, Ne, Kr, Xe, Ar, halocarbons and light hydrocarbons. The purifiers remove O<sub>2</sub>, H<sub>2</sub>, CO, CO<sub>2</sub> and H<sub>2</sub>O to sub-ppb (part-per-billion) levels; SO<sub>2</sub> to sub-ppt (part-per-trillion) levels.

## Features and Benefits

### Cost-effective

- Regenerable for low cost of ownership
- Gas purification improves process consistency, increases product yields and lengthens tool life
- Transforms low-purity gas into UHP grade, reducing process costs

### Environmentally Friendly

- Regenerable – eliminates disposal issues

### Process Protection

- Consistently delivers ultrapure gas
- Guards against bulk gas purifier breakthrough, impurity spikes from liquid storage tanks, cylinder changeouts and unexpected contaminants in the process
- Does not release hydrocarbons that may contaminate the process
- Low pressure drop across purifiers
- CE certified to the Pressure Equipment Directive (PED) and manufactured in an ISO 9001:2000 facility
- Backed by global service and support staff

### Safe and Simple to Use

- Easy to install
- Uses ambient temperature purification technology – no power or heat required
- No moving parts

## General Specifications

Materials of construction:	316L stainless steel, electropolished 10 Ra, except for the 45M model (Cr-Mo steel, SA 372, Grade F, Class 70)	
Gases purified:	N <sub>2</sub> , He, Ne, Kr, Ar, halocarbons, light hydrocarbons	
Outlet purity:	<1 ppb H <sub>2</sub> , CO and CO <sub>2</sub> ; <100 ppt H <sub>2</sub> O, O <sub>2</sub> ; the 45M model is <100 ppb for all contaminants	
Outlet particle filtration:	30KF to 75KF, 300KF to 10MH	0.003 µm 316L stainless steel
	100KF	0.003 µm nickel
	45M, 200M	20 µm 316L stainless steel
Media:	Nickel metallic/metal oxide	
Maximum differential pressure:	1379 kPa (200 PSID)	
Minimum operating pressure:	101 kPa (14.7 PSIA)	
Leak rating:	30KF to 10MH	1 × 10 <sup>-9</sup> atm-cc/sec
	45M	1 × 10 <sup>-3</sup> atm-cc/sec
	200M	4 × 10 <sup>-9</sup> atm-cc/sec
Maximum inlet challenge of contaminant to maintain product efficiency:	10 ppm (part-per-million)	
Lifetime:	One year at nominal flow rate with 1 ppm inlet challenge of moisture	
Maximum operating temperature:	65°C (149°F)	

## Operating Specifications

Model	Maximum Flow Rate (SLPM)	Nominal Flow Rate (SLPM)	Maximum Operating Pressure Purifier Only <sup>1</sup>	Maximum Operating Pressure Purifier with Options <sup>2</sup>	Pressure Drop <sup>3</sup>
35KF	1	0.5	19995 kPa (2900 PSIG)	1724 kPa (250 PSIG)	3.4 kPa (0.5 PSID)
70KF	3	1	19995 kPa (2900 PSIG)	1724 kPa (250 PSIG)	4.8 kPa (0.7 PSID)
100KF	20	2	6895 kPa (1000 PSIG)	1724 kPa (250 PSIG)	27.6 kPa (4 PSID)
300KF	50	7	4826 kPa (700 PSIG)	1724 kPa (250 PSIG)	34.5 kPa (5 PSID)
500KF	60	12	4826 kPa (700 PSIG)	1724 kPa (250 PSIG)	48.3 kPa (7 PSID)
500KFHP	60	12	19995 kPa (2900 PSIG)	19995 kPa (2900 PSIG)	48.3 kPa (7 PSID)
700KF	120	18	4826 kPa (700 PSIG)	1724 kPa (250 PSIG)	48.3 kPa (7 PSID)
2500KH	300	60	1724 kPa (250 PSIG)	1724 kPa (250 PSIG)	17.2 kPa (2.5 PSID)
5000K	500	130	1724 kPa (250 PSIG)	1724 kPa (250 PSIG)	62.1 kPa (9 PSID)
10MH	1000	220	1724 kPa (250 PSIG)	1724 kPa (250 PSIG)	1/2"– 62 kPa (9 PSID) 3/4"– 36.5 kPa (5.3 PSID)
45M <sup>4</sup>	5000	1100	20684 kPa (3000 PSIG)	20684 kPa (3000 PSIG)	<758 kPa (<110 PSID)
200M <sup>5</sup>	20000	3500	1379 kPa (200 PSIG)	1379 kPa (200 PSIG)	27.6 kPa (4 PSID)

### Drop-in Replacements for Waferpure® Purifiers

30KF (Micro)	1	0.5	19995 kPa (2900 PSIG)	1724 kPa (250 PSIG)	3.4 kPa (0.5 PSIG)
75KF (Mini-XL)	5	1	19995 kPa (2900 PSIG)	1724 kPa (250 PSIG)	10.3 kPa (1.5 PSIG)
300KF (Megaline)	50	7	4826 kPa (700 PSIG)	1724 kPa (250 PSIG)	34.5 kPa (5 PSIG)

<sup>1</sup> Do not use under vacuum. Minimum pressure should be 1 atm (14.7 PSIA).

<sup>2</sup> Pressure limited by standard valves, higher pressures available; please consult your local sales representative.

<sup>3</sup> Pressure drop at maximum flow rate and 90 PSIG (620 kPa) inlet pressure. For a detailed pressure drop curve and other pressures or flows, please consult your local sales representative or visit [www.entegris.com](http://www.entegris.com).

<sup>4</sup> Model only available for countries that recognize ASTM US standards and certifications; not CE certified; not a UHP product.

<sup>5</sup> Model only available for countries that recognize ASTM US standards; not currently CE certified; contact Entegris if needed for EU application.

All product information is subject to change without notice.

## Facility Specifications

Model	Fitting Sizes	Configuration (inlet/outlet)	Approximate Weight	Length	Diameter	Fitting Offset
35KF	1/4" face seal	male/male	0.3 kg (0.66 lb)	8.4 cm (3.31")	3.8 cm (1.5")	Centered
70KF	1/4" face seal	male/male	0.4 kg (0.88 lb)	11.4 cm (4.5")	3.8 cm (1.5")	Centered
100KF	1/4" face seal	male/male	0.5 kg (1.1 lb)	8.4 cm (3.31")	15.2 cm (6") <sup>6</sup>	1.12 cm (0.44")
300KF	1/4" face seal	male/male	1.8 kg (4 lb)	20.8 cm (8.2")	5.1 cm (2")	Centered
500KF	1/4" face seal	male/male	1.6 kg (3.5 lb)	20.2 cm (7.94")	7.6 cm (3")	Centered
500KFHP	1/4" face seal	male/male	2.5 kg (5.5 lb)	25.4 cm (10")	7.6 cm (3")	Centered
700KF	1/4" face seal	male/male	1.6 kg (3.5 lb)	25.4 cm (10")	7.6 cm (3")	Centered
2500KH	1/4" face seal	male/male	9.5 kg (20.9 lb)	43.9 cm (17.3")	10.2 cm (4")	Centered
	1/2" face seal	male/male	9.5 kg (20.9 lb)	44.7 cm (17.6")	10.2 cm (4")	Centered
5000K	1/2" face seal	female/male	15.5 kg (34.2 lb)	115.8 cm (45.6")	10.2 cm (4")	Centered
10MH	1/2" face seal	female/male	27 kg (59.5 lb)	97.4 cm (38.36")	15.2 cm (6")	Centered
	3/4" face seal	female/female	41 kg (90.3 lb)	143.3 cm (56.4")	15.2 cm (6")	Centered
45M	1/2" NPT	female/female	360 kg (794 lb)	147.3 cm (58")	24.4 cm (9.6")	Centered
200M	2" tube stub	—	454 kg (1000 lb)	165.9 cm (63.3") <sup>6</sup>	111.8 cm (44") <sup>7</sup>	81.8 cm (32.2") <sup>8</sup>

Drop-in Replacements for Waferpure® Purifiers						
30KF (Micro)	1/4" face seal	male/male	0.3 kg (0.66 lb)	8.4 cm (3.31")	3.8 cm (1.5")	0.97 cm (0.38")
75KF (Mini-XL)	1/4" face seal	male/male	0.4 kg (0.88 lb)	12.7 cm (5")	3.8 cm (1.5")	0.97 cm (0.38")
300KF (Megaline)	1/4" face seal	male/male	1.8 kg (4 lb)	20.8 cm (8.2")	5.1 cm (2")	Centered

<sup>6</sup> Height <sup>7</sup> Depth <sup>8</sup> Width

## Options

Model	Isolation Valves	GC 300 Manifold	3 Valve Bypass Manifold	5 Valve Bypass Manifold	4 Valve Changeover Manifold	8 Valve Changeover Manifold	Moisture Breakthrough Indicator <sup>9</sup>
35KF	Yes		Yes	Yes			Yes
70KF	Yes		Yes	Yes			Yes
100KF							Yes
300KF	Yes	Yes					Yes
500KF	Yes		Yes	Yes			Yes
500KFHP							Yes
700KF	Yes						Yes
2500KH	Yes		Yes	Yes	Yes	Yes	Yes
5000K	included						Yes
10MH	included		Yes		Yes		Yes
45M							
200M	included						

Drop-in Replacements for Waferpure® Purifiers							
30KF (Micro)	Yes		Yes	Yes			Yes
75KF (Mini-XL)	Yes		Yes	Yes			Yes
300KF (Megaline)	Yes	Yes					Yes


<sup>9</sup> External to purifier for models 30KF – 700KF.

# Ordering Information

## GateKeeper® Gas Purifiers

### Part Number

CE\* XXXXX X XX XXX R



Example: **CE2500KH18RR**  
 Model = 2500K  
 Filter = 0.003 μm (low pressure drop)  
 Gas series = Inert  
 Fitting = 1/2" face seal male-to-male  
 Additional processing = Regeneration

\* For all models except 45M and 200M. To order 45M and 200M:  
 45MI  
 SS200MI

Note: Not all models are available with all gas series or fittings; contact your salesperson for more information.  
 Note: For Mykrolis® replacement, specify 30K, 75K or 300K for model.  
 Note: This product is considered a dangerous good for shipping purposes under IATA/ICAO regulations.

For dimensional drawings, pressure drop curves and more, refer to the user manual or go to [www.entegris.com](http://www.entegris.com), click on Products and Services, and click on the link to Gas Microcontamination. An online “Product Wizard” is available to help you specify the ideal purifier for your application or you can contact our Gas Purification Specialists directly at 1-858-452-0124 or 1-800-511-9761 toll free in the U.S.

All products with the exception of the 45M, SS5000K and 200M models meet CE Directive 97/23/EC requirements.



Contact Customer Service to learn about our regeneration service.

## For More Information

Please call your Regional Customer Service Center today to learn what Entegris can do for you. Visit [www.entegris.com](http://www.entegris.com) and select “Regional Customer Service Centers” for the center nearest you.

## Terms and Conditions of Sale

All purchases are subject to Entegris’ “Terms and Conditions of Sale.” To view and print this information, visit Entegris’ website at [www.entegris.com](http://www.entegris.com) and select the Legal Notices link from the footer found on the home page.

Entegris®, Mykrolis®, Waferpure® and GateKeeper® are registered trademarks of Entegris, Inc.

---

### ENTEGRIS, INC.

Corporate Headquarters / 3500 Lyman Boulevard / Chaska, Minnesota 55318 USA  
Customer Service Tel. 952-556-4181 / Customer Service Fax 952-556-8022  
[www.entegris.com](http://www.entegris.com)